ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

# F88G24 8X8X24 N1 HC STRT SCT

*Hoffman Enclosures, Inc.*

| | |
|---|---|
| Catalog Number | F88G24 |
| Manufacturer | Hoffman Enclosures, Inc. |
| Description | Lay-In Wireway, Gray, Polyester Powder Paint, Steel, Hinged Cover, 8 In Overall Height, 24 In Overall Length, 8 In Overall Width, 18.5 LB |
| Weight per unit | 18.5 (lbs/each) |
| Product Category | Nema Type 1 Wireway & Fittings |

## Features

| | |
|---|---|
| ip rating | IP30 |
| Knockouts | FALSE |

## Material, Color, and Finish

| | |
|---|---|
| Color Code | ANSI 61 |
| Style | Liftoff Cover no Knockouts |

## Dimensions and Weight

| | |
|---|---|
| Height | 8 |
| Width | 8 |

## Descriptions

| | |
|---|---|
| Description | 8X8X24 N1 HC STRT SCT |
| extra long description | NVENT HOF F88G24 24.00in Straight S |
| Features | Lay-in Hinged-Cover Type 1 Straight Sections are used for enclosing wire and cable in wireway runs. Sections are completely open on one side so wires and cables can be laid in along wireway run. No pulling through of wires or cables prevents damage to insulation that often occurs in a pull-through wiring system. Sections are available in lengths from 12 inch to 120 inch, with or without knockouts. |

## Manufacturer Information

| | |
|---|---|
| Brand | Nvent Hoffman |
| GTIN | 00783510526108 |
| UPC | 783510526108 |

## Taxonomies, Classifications, and Categories

| | |
|---|---|
| Category Description | STEEL WIRE WAY JUNCTION BOXES |
| Type | Commercial Lay-in Hinged-Cover Type 1 Wireway;Straight Section |

## Packaging

| | |
|---|---|
| Carton | 1 |
| Weight Per each | 18.5 |

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

## Uses, Certifications, and Standards

| | |
|---|---|
| Application | Power Distribution |
| nema rating | 1 |