

## ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

7604 Gateway Blvd 77521-0000, TX Baytown Phone: 832-514-7819 Fax: 832-514-7820



Weight Per each

## **F88G24 8X8X24 N1 HC STRT SCT**

Hoffman Enclosures, Inc.

Catalog Number	F88G24
Manufacturer	Hoffman Enclosures, Inc.
Description	Lay-In Wireway, Gray, Polyester Powder Paint, Steel, Hinged Cover, 8 In Overall Height, 24 In Overall Length, 8 In Overall Width, 18.5 LB
Weight per unit	18.5 (lbs/each)
Product Category	Nema Type 1 Wireway & Fittings
Features	
ip rating	IP30
Knockouts	NO
Material, Color, and Finish	
Color Code	ANSI 61
Style	Liftoff Cover no Knockouts
Dimensions and Weight	
Height	8
Width	8
Descriptions	
Description	8X8X24 N1 HC STRT SCT
extra long description	NVENT HOF F88G24 24.00in Straight S
Features	Lay-in Hinged-Cover Type 1 Straight Sections are used for
	enclosing wire and cable in wireway runs. Sections are
	completely open on one side so wires and cables can be laid in
	along wireway run. No pulling through of wires or cables
	prevents damage to insulation that often occurs in a pull-throug
	wiring system. Sections are available in lengths from 12 inch to
	120 inch, with or without knockouts.
Manufacturer Information	
Brand	Nvent Hoffman
GTIN	00783510526108
UPC	783510526108
Taxonomies, Classifications, and	d Categories
Category Description	STEEL WIRE WAY JUNCTION BOXES
Туре	Straight Section
Packaging	
Carton	1

18.5

7604 Gateway Blvd 77521-0000, TX Baytown Phone: 832-514-7819 Fax: 832-514-7820

## **Uses, Certifications, and Standards**

Application	Power Distribution
nema rating	1 Indoor, electrical protection