



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



F8925L 2/0AWG SNGL Wire Bare Ferrule *Panduit Corporation*

Catalog Number	F8925L
Manufacturer	Panduit Corporation
Description	Ferrule, Non-Covered, 2/0 Awg Wire Range, 0.98(25.0MM) Length.
Weight per unit	0.0084 (lbs/each)
Product Category	Splicing & Terminating Kits

Features

insulation	Non-Insulated
Material	Copper
media	Yes
Wire Size	2/0

Material, Color, and Finish

Color	Metallic
Finish	Tinned

Descriptions

Description	2/0AWG SNGL WIRE BARE FERRULE
extra long description	PAN F89-25-L Pan-Term® F89-25-L Non
Long Description	Ferrule, Non-Covered, 2/0 AWG wire range, 0.98(25.0mm) length.
Product Type	Pan-Term® F89-25-L Non-Covered Ferrules

Manufacturer Information

Brand	Panduit®
GTIN	00074983650958
Manufacturers Part Number	F89-25-L
UPC	074983650958

Taxonomies, Classifications, and Categories

Type	Non-Covered Ferrule
------	---------------------

Availability

minimum qty	50
-------------	----

Packaging

Carton	50
Weight Per each	0.0084

Uses, Certifications, and Standards

Mounting	31/32
standard	DIN 46228, CSA C22.2 No. 291-14
Temperature Rating	302 Degrees Fahrenheit (150 Degrees Celsius)