



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

8110 Anderson Road Suite 100
33634-0000, FL Tampa
Phone: 813-934-6264
Fax: 000-000-0000

F96T12941HOSSECO 95W 96" 4100K T12 Fluorescent

Sylvania-Ledvance

Catalog Number	F96T12941HOSSECO
Manufacturer	Sylvania-Ledvance
Description	95W, 96 Inch Mol, T12 Ho (800MA) Rapid Start Supersaver Fluorescent Lamp, 4100K Color Temperature, 88 Cri. Vivid Color: High Cri Lamps For Color Critical Applications.
Weight per unit	1.4 (lbs/each)
Product Category	Linear Fluorescent Straight La

Features

amperage rating	Ballast Dependent
Base	Recessed Double Contact
bulb type	T12
lumens	8000
Shape	T12
total harmonic distortion	Ballast Dependent
Voltage Rating	Ballast Dependent

Material, Color, and Finish

color rendering index (cri)	88
color temperature	4100
Finish	Phosphor Coated

Descriptions

Description	95W 96" 4100K T12 FLUORESCENT
extra long description	SYL F96T12941HOSSECO/25037 F96T1294
Long Description	95W, 96 inch MOL, T12 HO (800mA) rapid start SUPERSAVER fluorescent lamp, 4100K color temperature, 88 CRI. VIVID Color: High CRI lamps for color critical applications.

Manufacturer Information

Brand	SYLVANIA
GTIN	00046135250378
Manufacturers Part Number	F96T12/941/HO/SS/ECO/25037
UPC	046135250378

Taxonomies, Classifications, and Categories

Category Description	Fluorescent
Type	FLUORESCENT

Packaging

Carton	1
Package	15
Weight Per each	1.41



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

8110 Anderson Road Suite 100
33634-0000, FL Tampa
Phone: 813-934-6264
Fax: 000-000-0000

Uses, Certifications, and Standards

Application

Commercial/Residential