



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## F96T12CWH0CT 110W T12 96" Cool White Cold Temp Ho 62 Cri R17D

*Ge By Current Lamps*

Catalog Number	F96T12CWH0CT
Manufacturer	Ge By Current Lamps
Description	Fluorescent Lamp, R17D Recessed Double Contact Base, T12 Bulb Shape, 60, 12000 H Average Life, 4100 K, Cool White, 800 Ma, 110 W, 3710 LM Brightness (Lumens), Soda Lime Housing Material, Shatter Resistant Coated, 1.5 In Diameter, 48.0 In Length, Instant;Rapid, 1.3 LB/Ea
Weight per unit	1.3 (lbs/each)
Product Category	Linear Fluorescent Straight La

### Features

Base	Recessed Double Contact (R17d)
lumens	8900.0
Wattage	110.0

### Material, Color, and Finish

color rendering index (cri)	60.0
-----------------------------	------

### Dimensions and Weight

Diameter	1.5
----------	-----

### Descriptions

Description	110W T12 96" COOL WHITE COLD TEMP HO 62 CRI R17D
extra long description	GEL F96T12/CW/HO/CT 11918 FLUORESC

### Manufacturer Information

Brand	Ge Traditional Lamps
GTIN	00043168119184
UPC	043168119184

### Taxonomies, Classifications, and Categories

Category Description	HIGH VOLUME FLUORESCENTS
----------------------	--------------------------

### Packaging

Carton	1
Package	15
Weight Per each	1.32