

ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr. 75964-0000, TX Nacogdoches Phone: 936-569-7941 Fax: 936-560-4685

F96T12CWH0CT 110W T12 96" Cool White Cold Temp Ho 62 Cri R17D
Ge By Current Lamps

Ge By Current Lamps	•
Catalog Number	F96T12CWH0CT
Manufacturer	Ge By Current Lamps
Description	Fluorescent Lamp, R17D Recessed Double Contact Base, T12 Bulb Shape, 60, 12000 H Average Life, 4100 K, Cool White, 800 Ma, 110 W, 3710 LM Brightness (Lumens), Soda Lime Housing Material, Shatter Resistant Coated, 1.5 In Diameter, 48.0 In Length, Instant; Rapid, 1.3 LB/Ea
Weight per unit	1.3 (lbs/each)
Product Category	Linear Fluorescent Straight La
Features	
Base	Recessed Double Contact (R17d)
lumens	8900
Wattage	110
Material, Color, and Finish	
color rendering index (cri)	60.0
Dimensions and Weight Diameter	1.5
Descriptions	
Description	110W T12 96" COOL WHITE COLD TEMP HO 62 CRI R17D
extra long description	GEL F96T12/CW/HO/CT 11918 FLUORESCE
Manufacturer Information	
Brand	Ge Traditional Lamps
GTIN	00043168119184
UPC	043168119184
Taxonomies, Classifications, and	Categories
Category Description	-
Packaging	
Carton	1
Package	15
Weight Per each	1.32