



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3315 Park Place
75462-0000, TX Paris
Phone: 903-784-1916
Fax: 903-784-0107

F96T12DH0COLD 115W T12 96" Daylight High Output Cold Temp 76 Cri

Sylvania-Ledvance

Catalog Number	F96T12DH0COLD
Manufacturer	Sylvania-Ledvance
Description	110W, 96"Mol, T12 Ho (800 Ma) Rapid Start Fluorescent Lamp, Daylightphosphor, 6500K Color Temperature, 73 Cri, Labeled For Cold Temperature Applications.
Weight per unit	1.4 (lbs/each)
Product Category	Linear Fluorescent Straight La

Features

amperage rating	Ballast Dependent
Base	Recessed Double Contact
bulb type	T12
lumens	7600 Initial Lumens at 25 Degrees C
Shape	T12
total harmonic distortion	Ballast Dependent
Voltage Rating	Ballast Dependent

Material, Color, and Finish

color rendering index (cri)	76
color temperature	6500

Descriptions

Description	115W T12 96" DAYLIGHT HIGH OUTPUT COLD TEMP 76 CRI
extra long description	SYL F96T12DHOCOLDTEMP/25135 F96T12D
Long Description	110W, 96"MOL, T12 HO (800 mA) rapid start fluorescent lamp, Daylightphosphor, 6500K color temperature, 73 CRI, labeled for cold temperature applications.

Manufacturer Information

Brand	SYLVANIA
GTIN	00046135251351
Manufacturers Part Number	F96T12/D/HO/COLD-TEMP/25135
UPC	046135251351

Taxonomies, Classifications, and Categories

Category Description	Fluorescent
Type	FLUORESCENT

Packaging

Carton	1
Package	15
Weight Per each	1.41

Uses, Certifications, and Standards

Application	Commercial/Residential
-------------	------------------------