



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



F96T12DSGN50H0 110W 96" T12 Recessed Double Contact 5000K Lamp

Sylvania-Ledvance

Catalog Number	F96T12DSGN50H0
Manufacturer	Sylvania-Ledvance
Description	OBS25164 110W, 96" Mol, T12 Ho (800 Ma) Rapid Start Fluorescent Lamp, Design 50 Phosphor, 5000K Color Temperature, 90 Cri. Vivid Color: High Cri Lamps For Color Critical Applications.
Weight per unit	1.4 (lbs/each)
Product Category	Lighting

Features

amperage rating	Ballast Dependent
average life	12000
Base	Recessed Double Contact
lumens	6450
Shape	T12
start type	Rapid Start
total harmonic distortion	Ballast Dependent
Voltage Rating	Ballast Dependent
Wattage	110

Material, Color, and Finish

color rendering index (cri)	90
color temperature	5000
Finish	Phosphor Coated

Dimensions and Weight

Diameter	1.5 in
Length	93.909

Descriptions

Description	110W 96" T12 RECESSED DOUBLE CONTACT 5000K LAMP
extra long description	SYL F96T12/DSGN50/HO/25164 F96T12DS
Long Description	OBS25164 110W, 96" MOL, T12 HO (800 mA) rapid start fluorescent lamp, Design 50 phosphor, 5000K color temperature, 90 CRI. VIVID Color: High CRI lamps for color critical applications.
Product Type	F96T12DSGN50HO 15/CS 1/Sku



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	SYLVANIA
GTIN	00046135251641
Manufacturers Part Number	F96T12/DSGN50/HO/25164
UPC	046135251641

Taxonomies, Classifications, and Categories

Category Description	Fluorescent
Type	FLUORESCENT

Availability

Status	Inactive
--------	----------

Packaging

Carton	1
Package	15
Weight Per each	1.41

Uses, Certifications, and Standards

Application	Commercial/Residential
-------------	------------------------