



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

121 S 39th Ave #100
85009-0000, AZ Phoenix
Phone: 480-372-4901
Fax: 480-372-4902



FB3DB Thermoplastic FL BX 25CU In RND DK Bronze CVR Dupl

Allied Moulded

Catalog Number	FB3DB
Manufacturer	Allied Moulded
Description	Floor Box Assembly, Injection Molded Black Polycarbonate (Box), Dark Bronze Plated Cast Brass (Cover), Closed Cell Rubber (Gasket), Nitrile (O-Ring), Plated Carbon Steel (Fastener), Galvanized Steel (Dust Plate), Steel (Wing Bracket) Material; 3 Inch
Weight per unit	1.7 (lbs/each)
Product Category	Floor Boxes & Accessories

Features

Cable Entry	(4) Molded-In Speed Klamps
Device Capacity	Duplex
Knockout Size	1/2 Inch Bottom
Material	Injection Molded Black Polycarbonate (Box), Dark Bronze Plated Cast Brass (Cover), Closed Cell Rubber (Gasket), Nitrile (O-Ring), Plated Carbon Steel (Fastener), Galvanized Steel (Dust Plate), Steel (Wing Bracket)
Number of Knockouts	2
Shape	Round

Dimensions and Weight

Height	3 INCH
--------	--------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

121 S 39th Ave #100
85009-0000, AZ Phoenix
Phone: 480-372-4901
Fax: 480-372-4902

Descriptions

Additional Information	Box Diameter 3.94 Inch; Cover Size 5.25 Inch Diameter x 0.217 Inch Thickness; Device Capacity 15 Amp 125 Volt NEMA 5-15R with Grounding; Application Floor Box Assembly for Residential Wood Floor; Applicable Standard ANSI, ISO 9001; WARNING: This product
Commodity Description	FLOOR BOXES & ACCESSORIES
Description	THERMOPLASTIC FL BX 25CU IN RND DK BRONZE CVR DUPL
extra long description	BLACK POLYCARBONATE (BOX), DARK BRONZE PLATED CAST BRASS (COVER), CLOSED CELL RUBBER (GASKET), NITRILE (O-RING), PLATED CARBON STEEL (FASTENER), GALVANIZED STEEL (DUST PLATE), STEEL (WING BRACKET) MATERIAL; 3.94 INCH; 3 INCH; ROUND SHAPE; WOOD FLOOR, OLD/NEW WORK INSTALLATION; UL, ANSI/UL 514C APPROVAL; METAL WING BRACKET/NON-METAL FLANGE FLOOR/CEILING COMPRESSION MOUNTING; 6 STANDARD PACKAGE; 24.5 CUBIC INCH CAPACITY; 1/2 INCH BOTTOM KNOCKOUT SIZE; 2 KNOCKOUT(S); MOLDED-IN SPEED CLAMP CABLE ENTRY; DUPLEX
Long Description	FLOOR BOX ASSEMBLY, INJECTION MOLDED BLACK POLYCARBONATE (BOX), DARK BRONZE PLATED CAST BRASS (COVER), CLOSED CELL RUBBER (GASKET), NITRILE (O-RING), PLATED CARBON STEEL (FASTENER), GALVANIZED STEEL (DUST PLATE), STEEL (WING BRACKET) MATERIAL; 3 INCH
Product Type	Floor Box Assembly

Manufacturer Information

Brand	Allied Moulded Products
GTIN	00085339996033
Manufacturers Part Number	FB-3DB
UPC	085339996033

Taxonomies, Classifications, and Categories

Category Description	FLOOR BOXES
----------------------	-------------

Packaging

Carton	1
Package	6
Standard Package	6
Weight Per each	1.666

Uses, Certifications, and Standards

Approval	UL 514C/714L
Capacity	24.5 Cubic Inch
Installation	Wood Floor, Old/New Work
Mounting	Wing Bracket/Non-Metal Flange Floor/Ceiling Compression