



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## FB3DB Thermoplastic FL BX 25CU In RND DK Bronze CVR Dupl

*Allied Moulded*

Catalog Number	FB3DB
Manufacturer	Allied Moulded
Description	Floor Box Assembly, Injection Molded Black Polycarbonate (Box), Dark Bronze Plated Cast Brass (Cover), Closed Cell Rubber (Gasket), Nitrile (O-Ring), Plated Carbon Steel (Fastener), Galvanized Steel (Dust Plate), Steel (Wing Bracket) Material; 3 Inch
Weight per unit	1.7 (lbs/each)
Product Category	Floor Boxes & Accessories

### Features

Cable Entry	(4) Molded-In Speed Klamps
Device Capacity	Duplex
Knockout Size	1/2 Inch Bottom
Material	Injection Molded Black Polycarbonate (Box), Dark Bronze Plated Cast Brass (Cover), Closed Cell Rubber (Gasket), Nitrile (O-Ring), Plated Carbon Steel (Fastener), Galvanized Steel (Dust Plate), Steel (Wing Bracket)
Number of Knockouts	2
Shape	Round

### Dimensions and Weight

Height	3 INCH
--------	--------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

### Additional Information

Box Diameter 3.94 Inch; Cover Size 5.25 Inch Diameter x 0.217 Inch Thickness; Device Capacity 15 Amp 125 Volt NEMA 5-15R with Grounding; Application Floor Box Assembly for Residential Wood Floor; Applicable Standard ANSI, ISO 9001; WARNING: This product

### Commodity Description

FLOOR BOXES & ACCESSORIES

### Description

THERMOPLASTIC FL BX 25CU IN RND DK BRONZE CVR DUPL

### extra long description

BLACK POLYCARBONATE (BOX), DARK BRONZE PLATED CAST BRASS (COVER), CLOSED CELL RUBBER (GASKET), NITRILE (O-RING), PLATED CARBON STEEL (FASTENER), GALVANIZED STEEL (DUST PLATE), STEEL (WING BRACKET) MATERIAL; 3.94 INCH; 3 INCH; ROUND SHAPE; WOOD FLOOR, OLD/NEW WORK INSTALLATION; UL, ANSI/UL 514C APPROVAL; METAL WING BRACKET/NON-METAL FLANGE FLOOR/CEILING COMPRESSION MOUNTING; 6 STANDARD PACKAGE; 24.5 CUBIC INCH CAPACITY; 1/2 INCH BOTTOM KNOCKOUT SIZE; 2 KNOCKOUT(S); MOLDED-IN SPEED CLAMP CABLE ENTRY; DUPLEX

### Long Description

FLOOR BOX ASSEMBLY, INJECTION MOLDED BLACK POLYCARBONATE (BOX), DARK BRONZE PLATED CAST BRASS (COVER), CLOSED CELL RUBBER (GASKET), NITRILE (O-RING), PLATED CARBON STEEL (FASTENER), GALVANIZED STEEL (DUST PLATE), STEEL (WING BRACKET) MATERIAL; 3 INCH

### Product Type

Floor Box Assembly

## Manufacturer Information

### Brand

Allied Moulded Products

### GTIN

00085339996033

### Manufacturers Part Number

FB-3DB

### UPC

085339996033

## Taxonomies, Classifications, and Categories

### Category Description

FLOOR BOXES

## Packaging

### Carton

1

### Package

6

### Standard Package

6

### Weight Per each

1.666

## Uses, Certifications, and Standards

### Approval

UL 514C/714L

### Capacity

24.5 Cubic Inch

### Installation

Wood Floor, Old/New Work

### Mounting

Wing Bracket/Non-Metal Flange Floor/Ceiling Compression