

CATALOG NUMBER	DESCRIPTION	UPC CODE	WEIGHT	CASE QTY	PALLET QTY	DISTRIBUTION CTRS				
						NJ	IL	TX	CA	GA
2RDI-332RP-UNV-EB81-U	3 LAMP, 2'X4' ROUND PERFORATED LAMP SHIELD, CENTER MOUNT, ELECTRONIC BALLAST, T8	662401732708	36	1	14	•	•		•	•
2RDI-332RP-UNV-EB82-U	3 LAMP, 2'X4' ROUND PERFORATED LAMP SHIELD, CENTER MOUNT, ELECTRONIC BALLAST (2), T8	622696299065	37	1	14		•			•
2RDI-332RP-UNV-EL4-EB81-U	3 LAMP, 2'X4' ROUND PERFORATED LAMP SHIELD, CENTER MOUNT, ELECTRONIC BALLAST, T8, W/EMERGENCY BATTERY	623961541681	39	1	14	•				
2RDI-332RP-UNV-L8735-A3/8-2/18G-EB81-U	3 LAMP, 2'X4' ROUND PERFORATED LAMP SHIELD, CENTER MOUNT, ELECTRONIC BALLAST, T8 W/LAMPS & FLEX	622697399627	42	1	12				•	
2RDI-332RP-UNV-L8735-EB82-U	2 LAMP 2'X4', ROUND PERFORATED LAMP SHIELDS, CENTER MOUNT, ELECTRONIC BALLAST (2), T8 W/LAMPS	622697686543	37	1	14				•	
<b>MASTER/SATELLITE</b>										
A-QCM-OP16-11-3/8-2RDI-332RP-UNV-L8735-EB82-U	3 LAMP, 2'X4', ROUND PERFORATED LAMP SHIELD, CENTER MOUNT, MASTER, ELECTRONIC BALLAST (2), T8 W/ LAMPS, W/ 11' FLEX	623961043314	23.36	1	12				•	
QCS-OP16-X-2RDI-332RP-L8735-LESS/IS/BAL-U	3 LAMP, 2'X4', ROUND PERFORATED LAMP SHIELD, CENTER MOUNT, T8 W/ LAMPS, REQUIRES MASTER ORDER SEPARATELY	623961043420	23.36	1	14				•	

## RECESSED WALL WASH RWW SERIES



1'X4'							DISTRIBUTION CTRS				
CATALOG NUMBER	DESCRIPTION	UPC CODE	WEIGHT	CASE QTY	PALLET QTY	NJ	IL	TX	CA	GA	
RWW-T1BX40MI-120V-EB51-U	2 BIAx LAMP, 4' RECESSED WALL WASH, ELECTRONIC BALLAST, W/SPECULAR LOW IRIDESCENT REFLECTOR, 120V	662401139576	14.6	1	40					•	

## RECESSED ACCESSORY

						DISTRIBUTION CTRS				
CATALOG NUMBER	DESCRIPTION	UPC CODE	WEIGHT	CASE QTY	PALLET QTY	NJ	IL	TX	CA	GA
A12-100-242G-U	2'X4' #12 LENS FOR G, GR8, GC & GC8 SERIES	662400106227	1.2	20	200		•		•	•
A12-125-24GC-U	2'X4' #12 .125 LENS FOR G, GR8, GC & GC8 SERIES	662400230144	2.8	5	150				•	•
DF-14W-U	1'X4' DRY WALL FRAME KIT	662401232949	2.2	1	130		•		•	•
DF-22W-U	2'X2' DRY WALL FRAME KIT	662401232963	1.95	1	130		•		•	
DF-24W-U	2'X4' DRY WALL FRAME KIT	662401232970	2.57	1	150		•	•	•	•
EQ-CLIP-U	T-BAR SAFETY CLIP FOR TROFFERS AND OVATION SERIES - ORDER 4 PER FIXTURE	662400107194	0.01	4500	81000				•	•
FCS-14W-U	1'X4' WHITE STEEL FLANGE KIT, FOR G, GR8, GC8 & GR5 SERIES	662400105992	4.2	1	130				•	
FCS-22W-U	2'X2' WHITE STEEL FLANGE KIT FOR G, GR8, GC8, GR5	662400105978	3.8	1	130					•
FCS-24W-U	2'X4' WHITE STEEL FLANGE KIT, FOR 2G, 2GR8, 2GC8 & 2GR5 SERIES	662400105985	4.8	1	200				•	•
2GR8-4-A W/SPGL FRM	2'X4' REPLACEMENT FRAME & LENS FOR 2G & 2GR8 SERIES	622697133917	4.4	6	36					•

## MODULAR SURFACE



1'X4'							DISTRIBUTION CTRS				
CATALOG NUMBER	DESCRIPTION	UPC CODE	WEIGHT	CASE QTY	PALLET QTY	NJ	IL	TX	CA	GA	
MC-232A-UNV-EB81-U	2 LAMP, 1'X4' SURFACE MODULAR, ELECTRONIC BALLAST, T8	662401620333	23.46	1	33		•			•	
<b>2'X2'</b>											
2M-2U6T8A-UNV-EB81-U	2 U-LAMP, 2'X2' SURFACE MODULAR, ELECTRONIC BALLAST, T8	662401879502	20.67	1	40	•	•			•	
<b>2'X4'</b>											
2M-332A-UNV-EB81-U	3 LAMP, 2'X4' SURFACE MODULAR, ELECTRONIC BALLAST, T8	662401793532	32	1	20		•				
2M-432A-UNV-EB81-U	4 LAMP, 2'X4' SURFACE MODULAR, ELECTRONIC BALLAST, T8	662401812486	33.2	1	20		•	•	•	•	

CATALOG NUMBER	DESCRIPTION	UPC CODE	WEIGHT	CASE QTY	PALLET QTY	DISTRIBUTION CTRS				
						NJ	IL	TX	CA	GA
2RDI-332RP-UNV-EB81-U	3 LAMP, 2'X4' ROUND PERFORATED LAMP SHIELD, CENTER MOUNT, ELECTRONIC BALLAST, T8	662401732708	36	1	14	•	•		•	•
2RDI-332RP-UNV-EB82-U	3 LAMP, 2'X4' ROUND PERFORATED LAMP SHIELD, CENTER MOUNT, ELECTRONIC BALLAST (2), T8	622696299065	37	1	14		•			•
2RDI-332RP-UNV-EL4-EB81-U	3 LAMP, 2'X4' ROUND PERFORATED LAMP SHIELD, CENTER MOUNT, ELECTRONIC BALLAST, T8, W/EMERGENCY BATTERY	623961541681	39	1	14	•				
2RDI-332RP-UNV-L8735-A3/8-2/18G-EB81-U	3 LAMP, 2'X4' ROUND PERFORATED LAMP SHIELD, CENTER MOUNT, ELECTRONIC BALLAST, T8 W/LAMPS & FLEX	622697399627	42	1	12				•	
2RDI-332RP-UNV-L8735-EB82-U	2 LAMP 2'X4', ROUND PERFORATED LAMP SHIELDS, CENTER MOUNT, ELECTRONIC BALLAST (2), T8 W/LAMPS	622697686543	37	1	14				•	
<b>MASTER/SATELLITE</b>										
A-QCM-OP16-11-3/8-2RDI-332RP-UNV-L8735-EB82-U	3 LAMP, 2'X4', ROUND PERFORATED LAMP SHIELD, CENTER MOUNT, MASTER, ELECTRONIC BALLAST (2), T8 W/ LAMPS, W/ 11' FLEX	623961043314	23.36	1	12				•	
QCS-OP16-X-2RDI-332RP-L8735-LESS/IS/BAL-U	3 LAMP, 2'X4', ROUND PERFORATED LAMP SHIELD, CENTER MOUNT, T8 W/ LAMPS, REQUIRES MASTER ORDER SEPARATELY	623961043420	23.36	1	14				•	

## RECESSED WALL WASH RWW SERIES



							NJ	IL	TX	CA	GA
<b>1'X4'</b>											
RWW-T1BX40MI-120V-EB51-U	2 BIAx LAMP, 4' RECESSED WALL WASH, ELECTRONIC BALLAST, W/SPECULAR LOW IRIDESCENT REFLECTOR, 120V	662401139576	14.6	1	40						•

## RECESSED ACCESSORY

							NJ	IL	TX	CA	GA
A12-100-242G-U	2'X4' #12 LENS FOR G, GR8, GC & GC8 SERIES	662400106227	1.2	20	200		•			•	•
A12-125-24GC-U	2'X4' #12 .125 LENS FOR G, GR8, GC & GC8 SERIES	662400230144	2.8	5	150					•	•
DF-14W-U	1'X4' DRY WALL FRAME KIT	662401232949	2.2	1	130		•			•	•
DF-22W-U	2'X2' DRY WALL FRAME KIT	662401232963	1.95	1	130		•			•	•
DF-24W-U	2'X4' DRY WALL FRAME KIT	662401232970	2.57	1	150		•	•		•	•
EQ-CLIP-U	T-BAR SAFETY CLIP FOR TROFFERS AND OVATION SERIES - ORDER 4 PER FIXTURE	662400107194	0.01	4500	81000					•	•
FCS-14W-U	1'X4' WHITE STEEL FLANGE KIT, FOR G, GR8, GC8 & GR5 SERIES	662400105992	4.2	1	130					•	
FCS-22W-U	2'X2' WHITE STEEL FLANGE KIT FOR G, GR8, GC8, GR5	662400105978	3.8	1	130						•
FCS-24W-U	2'X4' WHITE STEEL FLANGE KIT, FOR 2G, 2GR8, 2GC8 & 2GR5 SERIES	662400105985	4.8	1	200					•	•
2GR8-4-A W/SPGL FRM	2'X4' REPLACEMENT FRAME & LENS FOR 2G & 2GR8 SERIES	622697133917	4.4	6	36						•

## MODULAR SURFACE



							NJ	IL	TX	CA	GA
<b>1'X4'</b>											
MC-232A-UNV-EB81-U	2 LAMP, 1'X4' SURFACE MODULAR, ELECTRONIC BALLAST, T8	662401620333	23.46	1	33		•				•
<b>2'X2'</b>											
2M-2U6T8A-UNV-EB81-U	2 U-LAMP, 2'X2' SURFACE MODULAR, ELECTRONIC BALLAST, T8	662401879502	20.67	1	40	•	•				•
<b>2'X4'</b>											
2M-332A-UNV-EB81-U	3 LAMP, 2'X4' SURFACE MODULAR, ELECTRONIC BALLAST, T8	662401793532	32	1	20		•				
2M-432A-UNV-EB81-U	4 LAMP, 2'X4' SURFACE MODULAR, ELECTRONIC BALLAST, T8	662401812486	33.2	1	20		•	•		•	•