



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



FG250B *Delsited* Batt SMK Det W/Led *BRK Brands/Ademco/First Alert*

Catalog Number	FG250B
Manufacturer	BRK Brands/Ademco/First Alert
Description	Carbon Monoxide Alarm With Digital Display, 85 DB @ 10 FT Sound Level, Plastic, White, +40 °F Operating Temperature, +100 °F Operating Temperature, 4.25 In Diameter, 1.6 In Overall Height, Wall/Ceiling Mount, 4.8 Oz
Weight per unit	0.6800 (lbs/each)
Product Category	Smoke & Heat Detectors

Features

dimensions	5.6" diameter x 2.0" height
Operating Voltage	9V Carbon Zinc battery
Output Current	9V Carbon Zinc battery
Sensor Type	Ion
Temperature Range	40 Degree F (4 Degree C) to 100 Degree F (38 Degree C)

Material, Color, and Finish

Color	White
Enclosure Material	Plastic

Descriptions

Description	BATT SMK DET W/LED
extra long description	BRK FG250B 9V Battery Smoke Alarm

Manufacturer Information

GTIN	00029054003003
UPC	029054003003

Taxonomies, Classifications, and Categories

Category Description	SMOKE DETECTORS
Type	SMOKE ALARM

Packaging

Carton	1
Package	6
Weight Per each	0.68

Uses, Certifications, and Standards

environmental conditions	10 percent to 90 percent relative humidity (RH)
Mounting	mounts to wall or ceiling
standard	UL217