# Eaton FH09

## Catalog Number: FH09

Eaton A200/B100 heater, NEMA, Ambient .47-.50, .54-.58A, Non-Comp .44-.47, .53-.56A, Used with Starter Sizes 0,1, and 2, Type A and B, Thermal and Fast Trip

#### General specifications



Eaton A200/B100 heater

UPC

786678629148

**Product Height** 

0.8 in

**Product Weight** 

**CSA** Certified

**UL** Listed

0.03 lb

Catalog Number

FH09

Product Length/Depth

2.1 in

**Product Width** 

1.3 in

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the

date of shipment of the Product,

whichever occurs first.

Certifications Catalog Notes

Select heater coils based on full load current(FLA) shown on motor nameplate. Heater coils are rated to protect 40 degree C rise and a service factor of 1.15, Single-Phase requires 2 heaters,

Three-Phase Requires 3 heaters

Photo is representative



### default Taxonomy Attribute Label

Used with

Used with Starter Sizes 0,1, and 2

Design

NEMA

Full load current range

Ambient 0.47-0.50, 0.54-0.58 A, Non-Comp 0.44-0.47, 0.53-0.56

Overload relay

Type A and B

Trip type

Thermal and fast trip

#### Resources

#### Catalogs

Eaton's Volume 5—Motor Control and Protection

Installation instructions

Instructions for A200, A210, A250 size 6, two- or three-pole nonreversing or reversing motor controllers

Specifications and datasheets

Eaton Specification Sheet - FH09



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com

Reserved.

Eaton is a registered trademark.

All other trademarks are © 2024 Eaton. All Rights property of their respective owners.



Eaton.com/socialmedia