

# Eaton FH25

Catalog Number: FH25

Eaton A200/B100 heater, Used with Starter Sizes 0,1, and 2, A200/B100 Heater, NEMA, Ambient 2.16-2.35, 2.49-2.72A, Non-Comp 2.0-2.19, 2.44-2.67A, Used with Starter Sizes 0,1, and 2, Type A and B, Thermal and Fast Trip



## General specifications

### Product Name

Eaton A200/B100 heater

### Catalog Number

FH25

### UPC

786678629629

### Product Length/Depth

2.1 in

### Product Height

0.8 in

### Product Width

1.3 in

### Product Weight

0.03 lb

### Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Certifications

UL Listed  
CSA Certified

### Catalog Notes

Select heater coils based on full load current (FLA) shown on motor nameplate. Heater coils are rated to protect 40 degree C rise and a service factor of 1.15, Single-Phase requires 2 heaters, Three-Phase Requires 3 heaters

[Special features](#)

Used with Starter Sizes 0,1, and 2

[Type](#)

A200/B100 Heater

[Used with](#)

Used with Starter Sizes 0,1, and 2

[Design](#)

NEMA

[Full load current range](#)

Ambient 2.16-2.35, 2.49-2.72 A, Non-Comp 2.0-2.19, 2.44-2.67  
A

[Overload relay](#)

Type A and B

[Trip type](#)

Thermal and fast trip

[Catalogs](#)

[Eaton's Volume 5—Motor Control and Protection](#)

[Installation instructions](#)

[Instructions for A200, A210, A250 size 6, two- or three-pole non-reversing or reversing motor controllers](#)

[Specifications and datasheets](#)

[Eaton Specification Sheet - FH25](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)