# Eaton FH29

## Catalog Number: FH29

Eaton A200/B100 heater, Used with Starter Sizes 0,1, and 2, A200/B100 Heater, NEMA, Ambient 3.12-3.42, 3.61-3.95A, Non-Comp 2.90-3.17, 3.54-3.87A, Used with Starter Sizes 0,1, and 2, Type A and B, Thermal and Fast Trip

#### General specifications



Eaton A200/B100 heater

**UPC** 

786678629742

**Product Height** 

0.8 in

**Product Weight** 

0.03 lb

Catalog Number

FH29

Product Length/Depth

2.1 in

**Product Width** 

1.3 in

Warranty

Eaton Selling Policy 25-000, one (1) year

from the date of installation of the

Product or eighteen (18) months from the

date of shipment of the Product,

whichever occurs first.

Certifications

CSA Certified UL Listed Catalog Notes

Select heater coils based on full load current(FLA) shown on motor nameplate.

Heater coils are rated to protect 40 degree C rise and a service factor of 1.15, Single-Phase requires 2 heaters, Three-Phase Requires 3 heaters



### defaultTaxonomyAttributeLabel

#### Special features

Used with Starter Sizes 0,1, and 2

A200/B100 Heater

#### Used with

Used with Starter Sizes 0,1, and 2

#### Design

NEMA

#### Full load current range

Ambient 3.12-3.42, 3.61-3.95 A, Non-Comp 2.90-3.17, 3.54-3.87

#### Overload relay

Type A and B

#### Trip type

Thermal and fast trip

### Resources

#### Catalogs

Eaton's Volume 5—Motor Control and Protection

#### Installation instructions

Instructions for A200, A210, A250 size 6, two- or three-pole nonreversing or reversing motor controllers

#### Specifications and datasheets

Eaton Specification Sheet - FH29



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com

Reserved.

Eaton is a registered trademark.

All other trademarks are © 2024 Eaton. All Rights property of their respective owners.



Eaton.com/socialmedia