

Eaton FH41

Catalog Number: FH41

Eaton A200/B100 heater, Used with Starter Sizes 0,1, and 2, A200/B100 Heater, NEMA, Ambient 9.5-10.3, 10.9-11.9A, Non-Comp 8.8-9.5, 10.6-11.7A, Used with Starter Sizes 0,1, and 2, Type A and B, Thermal and Fast Trip

General specifications



Product Name

Eaton A200/B100 heater

UPC

786678670096

Product Height

0.8 in

Product Weight

0.03 lb

Certifications

CSA Certified

UL Listed

Catalog Number

FH41

Product Length/Depth

2.1 in

Product Width

1.3 in

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Catalog Notes

Select heater coils based on full load current (FLA) shown on motor nameplate. Heater coils are rated to protect 40 degree C rise and a service factor of 1.15, Single-Phase requires 2 heaters, Three-Phase Requires 3 heaters

Special features

Used with Starter Sizes 0,1, and 2

Type

A200/B100 Heater

Used with

Used with Starter Sizes 0,1, and 2

Design

NEMA

Full load current range

Ambient 9.5-10.3, 10.9-11.9 A, Non-Comp 8.8-9.5, 10.6-11.7 A

Overload relay

Type A and B

Trip type

Thermal and fast trip

Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

Installation instructions

[Instructions for A200, A210, A250 size 6, two- or three-pole non-reversing or reversing motor controllers](#)

Specifications and datasheets

[Eaton Specification Sheet - FH41](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)