

## A200/B100 Heater

**FH49**

**UPC:**786678670331

### **Dimensions:**

- **Height:** X
- **Length:** X
- **Width:** X

**Notes:**Select heater coils based on full load current(FLA) shown on motor nameplate. Heater coils are rated to protect 40 degree C rise and a service factor of 1.15, Single-Phase requires 2 heaters, Three-Phase Requires 3 heaters

### **Warranties:**

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### **Specifications:**

- **Special Features:** Used with Starter Sizes 1, and 2
- **Type:** A200/B100 Heater
- **Design:** NEMA
- **Full Load Current Range:** Ambient 19.9-21.7, 23.0-25.2A, Non-Comp 18.4-20.2, 22.0-23.9A
- **Overload Relay:** Type A and B
- **Trip Type:** Thermal and Fast Trip

### **Supporting documents:**

- [Eatons Volume 5-Motor Control and Protection](#)
- [Instructions for A200, A210, A250 size 6, two- or three-pole non-reversing or reversing motor controllers](#)
- [Eaton Specification Sheet - FH49](#)

### **Certifications:**

- UL Listed
- CSA Certified

**Product compliance:** No Data

---

© 2016 Eaton. All rights reserved.