# Eaton FH53

# Catalog Number: FH53

Eaton A200/B100 heater, Used with Starter Size 2, A200/B100 Heater, NEMA, Ambient 28.8-31.4, 33.4-36.4A, Non-Comp 26.7-29.1, 31.5-34.5A, Used with Starter Size 2, Type A and B, Thermal and Fast Trip



# General specifications

Product Name Eaton A200/B100 heater

UPC 786678670454

Product Height 0.8 in

Product Weight 0.03 lb

Certifications

**CSA** Certified

UL Listed

FH53 Product Length/Depth 2.1 in

Catalog Number

Product Width 1.3 in

## Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

# **Catalog Notes**

Select heater coils based on full load current(FLA) shown on motor nameplate. Heater coils are rated to protect 40 degree C rise and a service factor of 1.15, Single-Phase requires 2 heaters, Three-Phase Requires 3 heaters



# defaultTaxonomyAttributeLabel

## Special features

Used with Starter Size 2

# Туре

A200/B100 Heater

# Used with

Used with Starter Size 2

#### Design

NEMA

## Full load current range

Ambient 28.8-31.4, 33.4-36.4 A, Non-Comp 26.7-29.1, 31.5-34.5 A

# Overload relay

Type A and B

# Trip type

Thermal and fast trip

# Resources

Catalogs

Eaton's Volume 5-Motor Control and Protection

Installation instructions Instructions for A200, A210, A250 size 6, two- or three-pole nonreversing or reversing motor controllers

Specifications and datasheets Eaton Specification Sheet - FH53



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com © 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

Eaton.com All other trademarks are © 2024 Eaton. All Rights property of their respective Reserved. owners.



Eaton.com/socialmedia