

Eaton FH88

Catalog Number: FH88

Eaton A200/B100 heater, Used with A200 Starter Sizes 3 and 4, 3PH Only, A200 Heater, NEMA, Ambient 85-92A, Non-Comp 78-84A, Used with A200 Starter Sizes 3 and 4, 3PH Only, Type A and B, Thermal and Fast Trip

General specifications



Product Name

Eaton A200/B100 heater

UPC

786678671086

Product Height

0.8 in

Product Weight

0.06 lb

Certifications

CSA Certified

UL Listed

Catalog Number

FH88

Product Length/Depth

2.1 in

Product Width

1.1 in

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Catalog Notes

Select heater coils based on full load current (FLA) shown on motor nameplate. Heater coils are rated to protect 40 degree C rise and a service factor of 1.15, Single-Phase requires 2 heaters, Three-Phase Requires 3 heaters

Special features

Used with A200 Starter Sizes 3 & 4, 3-Phase Only

Type

A200 Heater

Used with

Used with A200 Starter Sizes 3 & 4, 3-Phase Only

Design

NEMA

Full load current range

Ambient 85-92 A, Non-Comp 78-84 A

Overload relay

Type A and B

Trip type

Thermal and fast trip

Catalogs

Eaton's Volume 5—Motor Control and Protection

Installation instructions

Instructions for A200, A210, A250 size 6, two- or three-pole non-reversing or reversing motor controllers

Specifications and datasheets

Eaton Specification Sheet - FH88

Warranty guides

Selling Policy 25-000 - Distribution and Control Products and Services



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia