

Eaton FH92

Catalog Number: FH92

Eaton A200/B100 heater, Used with A200 Starter Sizes 4, 3-Phase Only, A200 Heater, NEMA, Ambient 123-129A, Non-Comp 111-122A, Used with A200 Starter Sizes 4, 3-Phase Only, Type A and B, Thermal and Fast Trip

General specifications



Product Name

Eaton A200/B100 heater

UPC

786678671208

Product Height

1.3 in

Product Weight

0.1 lb

Certifications

UL Listed
CSA Certified

Catalog Number

FH92

Product Length/Depth

2.3 in

Product Width

2 in

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Catalog Notes

Select heater coils based on full load current (FLA) shown on motor nameplate. Heater coils are rated to protect 40 degree C rise and a service factor of 1.15, Single-Phase requires 2 heaters, Three-Phase Requires 3 heaters

defaultTaxonomyAttributeLabel

Special features

Used with A200 Starter Sizes 4, 3-Phase Only

Type

A200 Heater

Used with

Used with A200 Starter Sizes 4, 3-Phase Only

Design

NEMA

Full load current range

Ambient 123-129 A, Non-Comp 111-122 A

Overload relay

Type A and B

Trip type

Thermal and fast trip

Resources

Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

Installation instructions

[Instructions for A200, A210, A250 size 6, two- or three-pole non-reversing or reversing motor controllers](#)

Specifications and datasheets

[Eaton Specification Sheet - FH92](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)