

# HID Flood Lights

## 70 – 400W PS | HPS



### FL Series

9" Die Cast Rectangular



#### FEATURES

- Die Cast Aluminum Housing
- Hinged Face Frame
- One Piece Aluminum Reflector
- ½" Heavy Duty Knuckle
- UL Listed for Ground Mounting

#### ORDERING INFORMATION

CATALOG #	DESCRIPTION	VOLTS	BALLAST TYPE	LAMP
<b>Pulse Start</b>				
FL-70MHQPK	70 watt PS	Quad	HX-NPF	MH70/U/M
FL-100MHQPK	100 watt PS	Quad	HX-NPF	MH100/U/M
<b>High Pressure Sodium</b>				
FL-70HPK	70 watt HPS	120	R-NPF	C70S62/M
FL-100HPK	100 watt HPS	120	R-NPF	C100S54/M
FL-150HPK	150 watt HPS	120	R-NPF	C150S55/M



### FLM Series

9" Die Cast Square



#### FEATURES

- Die Cast Aluminum Housing
- Hinged Face Frame
- Tempered Glass Lens
- ½" Heavy Duty Knuckle or Slipfitter
- UL Listed for Ground Mounting

#### ORDERING INFORMATION

CATALOG #	DESCRIPTION	VOLTS	BALLAST TYPE	LAMP
<b>Pulse Start</b>				
FLM-70MHQPK	70 watt PS	Quad	HX-HPF	MH70/U/M
FLM-100MHQPK	100 watt PS	Quad	HX-HPF	MH100/U/M
FLM-150PQPK	150 watt PS	Quad	HX-HPF	MS150/U/M
<b>High Pressure Sodium</b>				
FLM-150HQPK	150 watt HPS	Quad	HX-HPF	C150S55/M



### FLDX Series

16" Die Cast Compact



#### FEATURES

- Die Cast Aluminum Housing
- Hinged Face Frame
- Trunion Mount
- Uses Standard Size Lamp
- Pre-wired with Cord

#### ORDERING INFORMATION

CATALOG #	DESCRIPTION	VOLTS	BALLAST TYPE	LAMP
<b>Pulse Start</b>				
FLDX-250PQPK	250 watt PS	Quad	CWA	MS250/H
FLDX-320PQPK	320 watt PS	Quad	CWA	MS320/H
FLDX-400PQPK	400 watt PS	Quad	CWA	MS400/H
FLDX-400P5PK	400 watt PS	5-Tap	CWA	MS400/H
<b>High Pressure Sodium</b>				
FLDX-400H5PK	400 watt HPS	5-Tap	CWA	C400S51

For Slipfitter Add Suffix "S"