





GE
Lighting

80892 - FLE11/2/R20XL827

GE Floodlight Soft White R20 - Facilities; Retail Display; Hospitality; Office; Restaurant

a product of
ecomagination



GENERAL CHARACTERISTICS

Lamp Type	Compact Fluorescent - Self-Ballasted
Bulb	R20
Base	Medium Screw (E26)
Equivalent Wattage	40.0 W
Rated Life	10000.0 hrs
Starting Temperature (MIN)	-15.0 °C
LEED-EB MR Credit	875 picograms Hg per mean lumen hour
Primary Application	Indoor Floodlight;Facilities;Retail Display;Hospitality;Office;Restaurant

PHOTOMETRIC CHARACTERISTICS

Initial Lumens	400.0
Nominal Initial Lumens per Watt	36
Color Temperature	2700.0 K
Color Rendering Index (CRI)	82.0

ELECTRICAL CHARACTERISTICS

Wattage	11.0
Voltage	120.0
Input Voltage	120.0 V

DIMENSIONS

Maximum Overall Length (MOL)	4.7000 in(119.4 mm)
Nominal Length	4.700 in(119.4 mm)

PRODUCT INFORMATION

Product Code	80892
Description	FLE11/2/R20XL827
Standard Package	Case
Standard Package GTIN	10043168808924
Standard Package Quantity	10
Sales Unit	Unit
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	10
UPC	043168808927

CAUTIONS & WARNINGS

Warning

- Risk of Electric Shock
 - Do not open - no user serviceable parts inside.
 - Do not use where directly exposed to water or outdoors without an enclosed fixture.