





GE
Lighting

80895 - FLE26/2/PAR38/XL

GE Floodlight PAR38 - Facilities; Retail Display; Hospitality; Office; Restaurant

a product of
ecomagination



CAUTIONS & WARNINGS

Warning

- Risk of Electric Shock
 - Do not open - no user serviceable parts inside.

GENERAL CHARACTERISTICS

Lamp Type	Compact Fluorescent - Self-Ballasted
Bulb	PAR38
Base	Medium Screw (E26)
Equivalent Wattage	100.0 W
Rated Life	10000.0 hrs
Starting Temperature (MIN)	-15.0 °C
Life in Years	9.1
LEED-EB MR Credit	269 picograms Hg per mean lumen hour
Primary Application	Pathway, Garden & Deck; Facilities; Retail Display; Hospitality; Office; Restaurant

PHOTOMETRIC CHARACTERISTICS

Initial Lumens	1300.0
Mean Lumens	1040.0
Nominal Initial Lumens per Watt	50
Color Temperature	2700.0 K
Color Rendering Index (CRI)	82.0

ELECTRICAL CHARACTERISTICS

Wattage	26.0
Input Voltage	120.0 V
Estimated Energy Cost per Year	3.13

DIMENSIONS

Maximum Overall Length (MOL)	5.6000 in(142.2 mm)
Nominal Length	5.500 in(139.7 mm)
Bulb Diameter (DIA)	4.750 in(120.6 mm)

PRODUCT INFORMATION

Product Code	80895
Description	FLE26/2/PAR38/XL
Standard Package	Case
Standard Package GTIN	10043168808955
Standard Package Quantity	6
Sales Unit	Unit
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	6
UPC	043168808958