



GE
Lighting

76137 - FLE26HT3/2GU24CD

GE T3



GENERAL CHARACTERISTICS

Lamp Type	Compact Fluorescent - Self-Ballasted
Bulb	T3
Base	GU24
Equivalent Wattage (NOM)	100.0 W
Rated Life (NOM)	10000.0 h
Life in Years (NOM)	9.1
Primary Application	Standard

PHOTOMETRIC CHARACTERISTICS

Initial Lumens (NOM)	1750.0
Mean Lumens (NOM)	1400.0
Nominal Initial Lumens per Watt (NOM)	67.3
Color Temperature (NOM)	2700.0 K
Color Rendering Index (CRI) (NOM)	80.0

ELECTRICAL CHARACTERISTICS

Wattage (NOM)	26.0
Voltage (NOM)	120.0
Estimated Energy Cost per Year (NOM)	3.13

DIMENSIONS

Maximum Overall Length (MOL) (NOM)	4.600 in(116.8 mm)
------------------------------------	--------------------

PRODUCT INFORMATION

Product Code	76137
Description	FLE26HT3/2GU24CD
Standard Package	Case
Standard Package GTIN	10043168761373
Standard Package Quantity	3
Sales Unit	Blister
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	3
UPC	043168761376