ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
1915 Turning Basin Suite 500
77029-0000, TX Houston
Phone: 713-675-6700
Fax: 713-675-6777



FLE70ESP8 70" Esp Damp Rated Fleming Ceiling Fan

Craftmade International I

Catalog Number	FLE70ESP8
Manufacturer	Craftmade International I
Description	Engineered For Large Indoor or Outdoor Spaces, The Captivating, Contemporary, Industrial Style and Energy Saving, 6-Speed, Reversible DC Motor Of The Indoor/Outdoor Fleming 70" Ceiling Fan Provides A Look and Feel That Delivers Maximum Performance With The Added Convenience Of A Dimmable Integrated Led Light With Optional Cover and Handheld Remote and Wall Controls.
Weight per unit	20.9 (lbs/each)
Product Category	20200605122656

Features

bulb type	LED
Category	Fans
Safety Rating	Damp
Voltage	120.00 FT

Material, Color, and Finish

Finish	Bronze/Dark
Style	Transitional

Descriptions

Description	70" ESP DAMP RATED FLEMING CEILING FAN
Long Description	Engineered for large indoor or outdoor spaces, the captivating, contemporary, industrial style and energy saving, 6-speed, reversible DC motor of the indoor/outdoor Fleming 70" ceiling fan provides a look and feel that delivers maximum performance with the added convenience of a dimmable integrated LED light with optional cover and handheld remote and wall controls.
Product Type	70"Ceiling Fan

Manufacturer Information

Brand	CRAFTMADE
GTIN	00647881211226
Manufacturers Part Number	FLE70ESP8
UPC	647881211226

Taxonomies, Classifications, and Categories

Category Description	Fuses & Fuse Accessories
Type	Damp Location

Availability

Manufacturer Status	Inactive

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
1915 Turning Basin Suite 500
77029-0000, TX Houston
Phone: 713-675-6700
Fax: 713-675-6777

Packaging

Carton	1
Weight Per each	20.94