



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



FLS10W30KBR 10W Led FLD Head BRZ 3K 950LM *Westgate MFG, Inc.*

Catalog Number	FLS10W30KBR
Manufacturer	Westgate MFG, Inc.
Description	Die-Cast Aluminum With Powder Coat Finish Cover Type Transparent PC White Reflector Driver Non-Dimmable Driver 13", #18 Awg Stranded Wires Power 10W Lumens 950LM Light Efficiency 75LM/W Voltage 100~277V, 50/60HZ Cri >80 Source Cob Beam Angle 100°, Ip Rating Wet Location Rotating Directional Hood
Weight per unit	2.4 (lbs/each)
Product Category	20170710110245

Features

bulb type	LED
Category	Landscape Ltg.
Safety Rating	ETL
Voltage	120.00 LBS

Material, Color, and Finish

Finish	Bronze/Dark
Style	Transitional

Descriptions

Description	10W LED FLD HEAD BRZ 3K 950LM
Long Description	Die-cast aluminum with powder coat finish Cover type Transparent PC White Reflector Driver Non-dimmable driver 13", #18 AWG stranded wires Power 10W Lumens 950LM Light Efficiency 75LM/W Voltage 100~277V, 50/60Hz CRI >80 Source COB Beam Angle 100°, IP Rating Wet Location Rotating directional hood
Product Type	Led Flood Head

Manufacturer Information

Brand	Westgate
GTIN	00845060048162
Manufacturers Part Number	FLS-10W-30K-BR
UPC	845060048162

Taxonomies, Classifications, and Categories

Category Description	Pole Line Construction Material & Equipment
Type	Spot Lights

Packaging

Carton	1
Weight Per each	2.36