

FEATURES & SPECIFICATIONS

INTENDED USE

Provides an LED lighting platform to deliver general ambient lighting for surface-mount ceiling applications. Light engine delivers long life and excellent color to ensure a quality, low-maintenance light installation.

CONSTRUCTION

Metal parts are die formed from code-gauge steel. Diffuser is constructed from matte white durable acrylic. Continuous side flanges on fixture body provide light trap and continuous diffuser support to prevent accidental opening and simplify maintenance.

Finish: Five-stage iron phosphate pretreatment assures superior paint adhesion and rust resistance. Painted parts finished with high-gloss, high-reflectivity baked white polyester enamel (low VOC).

OPTIC

Thermal formed diffuser is of highly transmissive material to minimize lamp image and provides highangle brightness control. One piece contemporary design wrap around diffuser soften appearance for improved aesthetics.

ELECTRICAL

Long-life LEDs, coupled with a high-efficiency driver, provide extended service life. Standard input = 45W, 111 lumens per watt. FMLL is rated to deliver L70 performance at 50,000 hours. Fixture operates at 120 volts, 60Hz and MVOLT (120-277) and is dimmable -120V Triac Dim. See suggested dimmer list on page 3.

LISTINGS

CSA certified to US and Canadian standards. Listed for damp locations. ENERGY STAR® certified.

WARRANT

5-year limited warranty. This is the only warranty provided and no other statements in this specification sheet create any warranty of any kind. All other express and implied warranties are disclaimed. Complete warranty terms located at:

https://www.acuitybrands.com/support/warranty/terms-and-conditions

NOTE: Actual performance may differ as a result of end-user environment and application. All values are design or typical values, measured under laboratory conditions at 25°C. Specifications subject to change without notice.

Catalog Number
Notes
Туре


Decorative Indoor

LED Litepuff Linear Low Profile Flush Mount

LINEAR LED







Specifications

Width: 14" (35.5) Length: 47-7/8 (121.7) Depth: 4 (10.16) Weight: 10.5 lbs

All dimensions are inches (centimeters) unless otherwise indicated.

For shortest lead times, configure products using boided options	ORDERING INFORMATION	For shortest lead times, configure products using bolded options .
---	----------------------	---

Series	Width	Voltage	CRI/Color temperature	CRI	Finish
FMLL	14IN 14"	(Blank) 120V MVOLT 120V-277V1	40K 4000K ² 30K 3000K	80CRI >80 90CRI >90	(Blank) White

Notes

1 MVOLT is not dimmable.


Example: FMLL 14IN 40K 80CRI

2 40K only available with 80CRI.

DECORATIVE INDOOR FML14

PHOTOMETRICS

Full photometric data report available within 2 weeks from request. Consult factory.




Coefficients of Utilization									
pf				2	20%				
рс		80%	•		70%			50%	
pw	70%	50%	30%	50%	30%	10%	50%	30%	10%
0	117	117	117	113	113	113	105	105	105
1	105	99	94	96	91	87	90	86	83
2	95	86	78	83	76	70	78	72	67
3	86	75	66	72	64	58	68	61	56
د 4	78	66	57	64	55	49	60	53	47
~ 25	72	59	49	57	48	42	54	46	40
^щ 6	66	53	44	51	43	36	48	41	35
7	61	48	39	46	38	32	44	36	31
8	57	43	35	42	34	28	40	33	28
9	53	40	31	39	31	26	37	30	25
10	50	37	29	36	28	23	34	27	22

Zonal Lumen Summary							
1%	Zone	Lumens	% Lamp	% Fixture			
)5	0° - 30°	763	21.9	21.9			
3	0° - 40°	1253	36.0	36.0			
7	0° - 60°	2254	64.8	64.8			
6	0° - 90°	3122	89.8	89.8			
7	90° - 120°	235	6.8	6.8			
0	90° - 130°	278	8.0	8.0			
5	90° - 150°	330	9.5	9.5			
1	90° - 180°	355	10.2	10.2			
8	0° - 180°	3478	100.0	100.0			
5							
2							

LIGHTING FACTS





LIGHTING FACTS

