



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



FMVA13LWYUNV3476 91-95W 347-400V 3/4" NPT Yoked Led Flood *Crouse-Hinds*

Catalog Number	FMVA13LWYUNV3476
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series Champ Fmva Led Floodlight, Warm White, Dimmable Driver, 3/4" Entry, 400W Equivalent, Heat and Impact Resistant Glass Lens, 13000 Lumens, 143 LM/W, Die Cast Aluminum, Yoke Mount, 347-480 Vac, 95W, 7X6 Optics
Weight per unit	32.5 (lbs/each)
Product Category	20191219102250

Descriptions

Description	91-95W 347-400V 3/4" NPT YOKED LED FLOOD
extra long description	CRS-H FMVA13LWY-UNV34-76 LED FLOOD
Features	Crouse-Hinds series Champ FMVA LED floodlights are designed to provide full-spectrum, crisp, white light in Class I and Class II hazardous areas. Eleven versions of the Champ FMVA are available, ranging from 3,000 to 50,000 lumens, providing a reliable and long-life solution for a wide range of floodlighting applications. Champ FMVA LED floodlights are certified for use in NEC, CEC and IEC hazardous locations, providing a single solution for applications around the world. These floodlights are ideal for
Long Description	Eaton Crouse-Hinds series Champ FMVA LED floodlight, Warm white, Dimmable driver, 3/4" entry, 400W equivalent, Heat and impact resistant glass lens, 13000 lumens, 143 lm/W, Die cast aluminum, Yoke mount, 347-480 Vac, 95W, 7x6 optics
Product Type	Led Flood Warm Glass Lens 347-480 Vac

Manufacturer Information

Brand	Eaton
GTIN	00662276885820
Manufacturers Part Number	FMVA13LWY-UNV34-76
UPC	662276885820

Taxonomies, Classifications, and Categories

Category Description	LED HAZARDOUS LOCATION & VAPOR TIGHT LIGHTING
----------------------	---

Availability

Status	Inactive
--------	----------

Packaging

Carton	1
Weight Per each	32.5