

# Eaton FNA-3

Catalog Number: FNA-3

Eaton Bussmann series FNA fuse, Time-delay fuse, Inductive load circuits, Electronic circuits, 3 A, Dual, Non-indicating, Ferrule end x ferrule end, 200 kAIC at 250 Vac|10 kAIC at 125 Vac, Silver-plated pin, Standard, 250 V



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton Bussmann series FNA fuse	FNA-3
<b>UPC</b>	<b>Product Length/Depth</b>
051712713535	1.5 in
<b>Product Height</b>	<b>Product Width</b>
0.406 in	0.406 in
<b>Product Weight</b>	<b>Warranty</b>
1.5 lb	Not Applicable
<b>Compliances</b>	
CE Marked	

## Electrical rating

### Amperage Rating

3 A

### Interrupt rating

10 kAIC at 125 Vac

200 kAIC at 250 Vac

### Voltage rating

250 V

## Physical details

### Material

Silver-plated pin

### Number of elements

Dual

### Packaging type

Standard

## General information

### Connection

Ferrule end x ferrule end

### Fuse indicator

Non-indicating

### Special features

Superior overload and cycling capabilities

## Resources

### Catalogs

[Bussmann series complete full line catalog no. 1007](#)

### Specifications and datasheets

[Eaton Specification Sheet - FNA-3](#)

### Technical data sheets

[FNA-3~FUSETRON DUAL-ELEMENT INDICATING](#)

### Technical service bulletins

[Datasheet - FNQ-30](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)