Eaton FNM-1

FNM-1

Catalog Number: FNM-1

Eaton Bussmann series FNM fuse, Time-delay, 1 A, Dual, Nonindicating, Ferrule end x ferrule end, 35 AIC at 250 Vac|10 kAIC at 125 Vac, Nickel-plated bronze endcap, Standard, 250 V

General specifications

Product Name

Eaton Bussmann series FNM fuse

UPC

051712520102

Product Height

0.41 in

Product Weight

0.2 lb

Compliances **CE Marked**

RoHS Compliant

Catalog Number

FNM-1

Product Length/Depth

1.5 in

Product Width

0.41 in

Warranty

Not Applicable



Electrical rating

Amperage Rating

1 A

Interrupt rating

35 AIC at 250 Vac 10 kAIC at 125 Vac

Voltage rating

250 V

Resources

Catalogs

Bussmann series complete full line catalog no. 1007

Multimedia

Bussmann series Fuseology

Specifications and datasheets

Eaton Specification Sheet - FNM-1

Technical data sheets

FNM-1~BUSS MIDGET FUSE

Technical service bulletins

Datasheet - FNQ-30

Physical details

Material

Nickel-plated bronze endcap

Number of elements

Dual

Packaging type

Standard

General information

Connection

Ferrule end x ferrule end

Fuse indicator

Non-indicating

Special features

Superior overload and cycling capabilities



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com

Reserved.

Eaton is a registered trademark.

All other trademarks are © 2024 Eaton. All Rights property of their respective owners.



Eaton.com/socialmedia