

Eaton FNM-30

Catalog Number: FNM-30

Eaton Bussmann series FNM fuse, Time-delay, 30 A, Dual, Non-indicating, Ferrule end x ferrule end, 10 kAIC at 250 Vac, Nickel-plated bronze endcap, Standard, 250 V



General specifications

| | |
|--------------------------------|-----------------------------|
| Product Name | Catalog Number |
| Eaton Bussmann series FNM fuse | FNM-30 |
| UPC | EAN |
| 051712523004 | 5027590060264 |
| Product Length/Depth | Product Height |
| 0.39 in | 1.44 in |
| Product Width | Product Weight |
| 0.39 in | 0.2 lb |
| Warranty | Compliances |
| Not Applicable | CE Marked RoHS Compliant |

Electrical rating

Amperage Rating

30 A

Interrupt rating

10 kAIC at 250 Vac

Voltage rating

250 V

Physical details

Material

Nickel-plated bronze endcap

Number of elements

Dual

Packaging type

Standard

General information

Connection

Ferrule end x ferrule end

Fuse indicator

Non-indicating

Special features

Superior overload and cycling capabilities

Resources

Catalogs

[Bussmann series complete full line catalog no. 1007](#)

Multimedia

[Bussmann series Fuseology](#)

Specifications and datasheets

[Eaton Specification Sheet - FNM-30](#)

Technical data sheets

[FNM-30~BUSS MIDGET FUSE](#)

Technical service bulletins

[Datasheet - FNQ-30](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia