

Eaton FNQ-1/10

Catalog Number: FNQ-1/10

Eaton Bussmann series FNQ fuse, Time-delay, Motor control transformers, Circuits with in-rush currents, 0.1 A, Non-indicating, Ferrule end x ferrule end, 10 kAIC at 500 Vac, Nickel-plated bronze endcap, Standard, 500 V



General specifications

Product Name	Catalog Number
Eaton Bussmann series FNQ fuse	FNQ-1/10
UPC	EAN
051712786164	5027590449892
Product Length/Depth	Product Height
0.41 in	1.5 in
Product Width	Product Weight
0.41 in	0.175 lb
Warranty	Compliances
Not Applicable	CE Marked
	RoHS Compliant

Electrical rating

Amperage Rating

0.1 A

Interrupt rating

10 kAIC at 500 Vac

Voltage rating

500 V

Physical details

Material

Nickel-plated bronze endcap

Packaging type

Standard

General information

Connection

Ferrule end x ferrule end

Fuse indicator

Non-indicating

Special features

Non-indicating

Resources

Catalogs

[Bussmann series complete full line catalog no. 1007](#)

Multimedia

[Bussmann series Fuseology](#)

Specifications and datasheets

[Eaton Specification Sheet - FNQ-1/10](#)

Technical data sheets

[FNQ-1/10~FNQ-1-10~BUSS MIDGET FUSE](#)