

# Eaton FNQ-1-1/2

Catalog Number: FNQ-1-1/2

Eaton Bussmann series FNQ fuse, Time-delay, Motor control transformers, Circuits with in-rush currents, 1.5 A, Non-indicating, Ferrule end x ferrule end, 10 kAIC at 500 Vac, Nickel-plated bronze endcap, Standard, 500 V

## General specifications

Product Name	Catalog Number
Eaton Bussmann series FNQ fuse	FNQ-1-1/2
UPC	Product Length/Depth
051712786249	1.5 in
Product Height	Product Width
0.41 in	0.41 in
Product Weight	Warranty
0.175 lb	Not Applicable
Compliances	
CE Marked	
RoHS Compliant	

## Electrical rating

### Amperage Rating

1.5 A

### Interrupt rating

10 kAIC at 500 Vac

### Voltage rating

500 V

## Physical details

### Material

Nickel-plated bronze endcap

### Packaging type

Standard

## General information

### Connection

Ferrule end x ferrule end

### Fuse indicator

Non-indicating

### Special features

Non-indicating

## Resources

### Catalogs

[Bussmann series complete full line catalog no. 1007](#)

### Multimedia

[Bussmann series Fuseology](#)

### Specifications and datasheets

[Eaton Specification Sheet - FNQ-1-1/2](#)

### Technical data sheets

[FNQ-1-1/2~FNQ-1-1-2~BUSS MIDGET FUSE](#)