ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
3507 N Van Buren Bypass
73701-0000, OK Enid
Phone: 580-701-6818
Fax: 580-234-5655



FNQ4 4A 500V TD CT Midget Fuse

Bussmann Fuses

Catalog Number	FNQ4
Manufacturer	Bussmann Fuses
Description	Eaton Bussmann Series FNQ Fuse, Time-Delay, Motor Control Transformers, Circuits With In-Rush Currents, 4 A, Non-Indicating, Ferrule End X Ferrule End, 10 Kaic At 500 Vac, Nickel-Plated Bronze Endcap, Standard, 500 V
Weight per unit	0.0200 (lbs/each)
Product Category	Small Dimension Fuses

Features

amperage rating	4 Amp
class	Supplemental
connection	Ferrule End X Ferrule End
dimensions	0.4100 IN X 0.4100 IN X 1.5000 IN
interrupt rating	10000 Amp (RMS Symmetrical)
Material	Nickel-plated bronze endcap
Voltage Rating	500 VAC

Dimensions and Weight

Size	13/32 In Diameter X 1-1/2 In Length

Descriptions

Description	4A 500V TD CT MIDGET FUSE
extra long description	BUS FNQ-4 BUSS MIDGET FUSE
Features	Bussmann offers the broadest selection of Supplemental and Midget fuses in both time-delay and fast-acting designs with voltages as high as 600Vac and 600Vdc.
Long Description	Eaton Bussmann series FNQ fuse, Time-delay, Motor control transformers, Circuits with in-rush currents, 4 A, Non-indicating, Ferrule end x ferrule end, 10 kAIC at 500 Vac, Nickel-plated bronze endcap, Standard, 500 V
Product Type	Buss Midget Fuse
Special Features	Nickel Plated Brass Endcap

Manufacturer Information

Brand	Eaton
GTIN	00051712786041
Manufacturers Part Number	FNQ-4
UPC	051712786041

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
3507 N Van Buren Bypass
73701-0000, OK Enid
Phone: 580-701-6818
Fax: 580-234-5655

Taxonomies, Classifications, and Categories

Category Description	MIDGET FUSES
Type	FUSE

Packaging

Carton	10
Weight Per each	0.02

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Facility: Safety and Security Systems
standard	RoHS Compliant,CE Marked