

Eaton FNQ-4

Catalog Number: FNQ-4

Eaton Bussmann series FNQ fuse, Time-delay, Motor control transformers, Circuits with in-rush currents, 4 A, Non-indicating, Ferrule end x ferrule end, 10 kAIC at 500 Vac, Nickel-plated bronze endcap, Standard, 500 V



General specifications

Product Name	Catalog Number
Eaton Bussmann series FNQ fuse	FNQ-4
UPC	EAN
051712786041	5027590060547
Product Length/Depth	Product Height
0.41 in	1.5 in
Product Width	Product Weight
0.41 in	0.175 lb
Warranty	Compliances
Not Applicable	CE Marked RoHS Compliant

Electrical rating

Amperage Rating

4 A

Interrupt rating

10 kAIC at 500 Vac

Voltage rating

500 V

Physical details

Material

Nickel-plated bronze endcap

Packaging type

Standard

General information

Connection

Ferrule end x ferrule end

Fuse indicator

Non-indicating

Special features

Non-indicating

Resources

Catalogs

Bussmann series full line catalog 1007, section 01- low voltage branch circuit fuses

[FNQ-4~BUSS MIDGET FUSE](#)

Bussmann series complete full line catalog no. 1007

Multimedia

[Bussmann series Fuseology](#)

Specifications and datasheets

[Eaton Specification Sheet - FNQ-4](#)

Technical service bulletins

[Datasheet - FNQ-30](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)