

Eaton FNQ-6-1/4

Catalog Number: FNQ-6-1/4

Eaton Bussmann series FNQ fuse, Time-delay, Motor control transformers, Circuits with in-rush currents, 6.25 A, Non-indicating, Ferrule end x ferrule end, 10 kAIC at 500 Vac, Nickel-plated bronze endcap, Standard, 500 V



General specifications

Product Name	Catalog Number
Eaton Bussmann series FNQ fuse	FNQ-6-1/4
UPC	EAN
051712786317	5027590450041
Product Length/Depth	Product Height
0.41 in	1.5 in
Product Width	Product Weight
0.41 in	0.175 lb
Warranty	Compliances
Not Applicable	CE Marked
	RoHS Compliant

Electrical rating

Amperage Rating

6.25A

Interrupt rating

10 kAIC at 500 Vac

Voltage rating

500 V

Physical details

Material

Nickel-plated bronze endcap

Packaging type

Standard

General information

Connection

Ferrule end x ferrule end

Fuse indicator

Non-indicating

Resources

Catalogs

[Bussmann series complete full line catalog no. 1007](#)

Multimedia

[Bussmann series Fuseology](#)

Specifications and datasheets

[Eaton Specification Sheet - FNQ-6-1/4](#)

Technical data sheets

[FNQ-6-1/4~FNQ-6-1-4~BUSS MIDGET FUSE](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)