Eaton FNQ-R-1/2

Catalog Number: FNQ-R-1/2

Eaton Bussmann series FNQ-R fuse, 0.5 A, Class CC, Nonindicating, Ferrule end x ferrule end, 12 sec at 200%, 200 kAIC, Melamine tube, Standard, 600 V



General specifications

Product Name

Eaton Bussmann series FNQ-R fuse

051712147019

Product Height 0.41 in

Product Weight 0.15 lb

Compliances CE Marked RoHS Compliant Catalog Number FNQ-R-1/2

Product Length/Depth 1.5 in

Product Width 0.41 in

Warranty Not Applicable



Electrical Ratings

Amperage Rating

0.5 A

Voltage rating

600 V

General Information

Application

Line protection, small control transformers, industrial control, branch circuits

Connection

Ferrule end x ferrule end

Special features

Rejection style

Physical Details

Туре

Current-limiting high inrush time-delay fuse

Resources

Catalogs

Bussmann series complete full line catalog no. 1007

Multimedia

Bussmann series Fuseology

Specifications and datasheets Eaton Specification Sheet - FNQ-R-1/2

Technical data sheets FNQ-R-1/2~FNQ-R-1-2~CLASS CC TIME DELAY



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com © 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

Eaton.comAll other trademarks are© 2024 Eaton. All Rightsproperty of their respectiveReserved.owners.



Eaton.com/socialmedia