

# ELLIOTT ELECTRIC SUPPLY 1308 East 4th Street 79720-0000, TX Big Spring Phone: 432-264-0316 Fax: 432-264-0483



### FNQR10 10A 600V TD Class CC Fuse

Bussmann Fuses

Catalog Number	FNQR10	
Manufacturer	Bussmann Fuses	
Description	Fuse, Time Delay Fuse Speed, Class CC Fuse, 12 S @ 200%	
	Response Time, Ferrule End X Ferrule End Connection, 10 A, 600	
	V Ac, Melamine Material, 0.41 In Diameter, 1.5 In Overall Length,	
	0.02 LB	
Weight per unit	0.0200 (lbs/each)	
Product Category	Small Dimension Fuses	

### **Features**

amperage rating	10
connection	Ferrule End X Ferrule End
dimensions	1.5000 IN X 0.4100 IN X 0.4100 IN
media	Vos

# **Dimensions and Weight**

Size 13/32 In Diameter X 1-1/2 In Length

## **Descriptions**

Description	10A 600V TD CLASS CC FUSE
extra long description	BUSS FNQ-R-10 CLASS CC TIME DELAY
Features	Bussmann's Class CC fuses set the standard in Class CC fuse performance in the industry. Recognized for their superior performance, Bussmann has the right product for your circuit and equipment protection needs. These branch circuit rated, 600v, 200,000a IR fuses offer exceptional protection in the smallest package of any UL class of fuses. Choose from the ultimate protection provided by our Low Peak LP-CC fuses, the time delay of our FNQ-R's for your control transformer and similar control applications or
Special Features	Rejection Style

### Manufacturer Information

Brand	Eaton
GTIN	00051712497091
UPC	051712497091

# **Taxonomies, Classifications, and Categories**

Category Description	MIDGET FUSES
Туре	FUSE

# **Packaging**

Carton	10
Weight Per each	0.02

1308 East 4th Street 79720-0000, TX Big Spring Phone: 432-264-0316 Fax: 432-264-0483

Uses, Certifications, and Standards		
standard	PoHS Compliant CF Marked	