Eaton FNQ-R-1-1/2

Catalog Number: FNQ-R-1-1/2

Eaton Bussmann series FNQ-R fuse, 1.5 A, Class CC, Non-indicating, Ferrule end x ferrule end, 12 sec at 200%, 200 kAIC, Melamine tube, Standard, $600\ V$

General specifications



Catalog Number

Eaton Bussmann series FNQ-R fuse

FNQ-R-1-1/2

UPC

EAN

051712147057

5027590449625

Product Length/Depth

Product Height 1.5 in

0.41 in

Product Width

Not Applicable

Product Weight 0.15 lb

0.41 in

Compliances

Warranty

CE Marked

CE

RoHS Compliant





Electrical Ratings

Amperage Rating

1.5 A

Voltage rating

600 V

General Information

Application

Line protection, small control transformers, industrial control, branch circuits

Connection

Ferrule end x ferrule end

Special features

Rejection style

Physical Details

Type

Current-limiting high inrush time-delay fuse

Resources

Catalogs

Bussmann series complete full line catalog no. 1007

Multimedia

Bussmann series Fuseology

Specifications and datasheets

Eaton Specification Sheet - FNQ-R-1-1/2

Technical data sheets

FNQ-R-1-1/2~FNQ-R-1-1-2~CLASS CC TIME DELAY



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com

Reserved.

Eaton is a registered trademark.

All other trademarks are © 2024 Eaton. All Rights property of their respective owners.



Eaton.com/socialmedia