# Eaton FNQ-R-2-1/2

## Catalog Number: FNQ-R-2-1/2

Eaton Bussmann series FNQ-R fuse, 2.5 A, Class CC, Non-indicating, Ferrule end x ferrule end, 12 sec at 200%, 200 kAIC, Melamine tube, Standard, 600 V

## General specifications

Not Applicable

Product Name Catalog Number

Eaton Bussmann series FNQ-R fuse FNQ-R-2-1/2

UPC EAN

051712147071 5027590449694

Product Length/Depth Product Height

0.41 in 1.5 in

Product Width Product Weight

0.41 in 0.15 lb

Warranty Compliances

RoHS Compliant

**CE Marked** 



## **Electrical Ratings**

**Amperage Rating** 

2.5 A

Voltage rating

600 V

## General Information

#### Application

Line protection, small control transformers, industrial control, branch circuits

#### Connection

Ferrule end x ferrule end

## Special features

Rejection style

## Physical Details

## Type

Current-limiting high inrush time-delay fuse

## Resources

## Catalogs

Bussmann series complete full line catalog no. 1007

#### Multimedia

Bussmann series Fuseology

## Specifications and datasheets

Eaton Specification Sheet - FNQ-R-2-1/2

## Technical data sheets

FNQ-R-2-1/2~FNQ-R-2-1-2~CLASS CC TIME DELAY



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com

Reserved.

Eaton is a registered trademark.

All other trademarks are © 2023 Eaton. All Rights property of their respective owners.



Eaton.com/socialmedia