# Eaton FNQ-R-25

## Catalog Number: FNQ-R-25

Eaton Bussmann series FNQ-R fuse, 25 A, Class CC, Non-indicating, Ferrule end x ferrule end, 12 sec at 200%, 200 kAlC, Melamine tube, Standard, 600 V

## General specifications

Product Name

Catalog Number

Eaton Bussmann series FNQ-R fuse

FNQ-R-25

UPC

EAN

051712497138

5027590449724

Product Length/Depth

Product Height 1.5 in

0.41 in

Product Width

Product Weight 0.15 lb

0.41 in

Compliances

Warranty
Not Applicable

CE Marked

RoHS Compliant





## **Electrical Ratings**

Amperage Rating

25 A

Voltage rating

600 V

## General Information

#### Application

Line protection, small control transformers, industrial control, branch circuits

#### Connection

Ferrule end x ferrule end

## Special features

Rejection style

## Physical Details

## Type

Current-limiting high inrush time-delay fuse

## Resources

## Catalogs

Bussmann series complete full line catalog no. 1007

#### Multimedia

Bussmann series Fuseology

## Specifications and datasheets

Eaton Specification Sheet - FNQ-R-25

#### Technical data sheets

FNQ-R-25~CLASS CC TIME DELAY REJECTION FUSE

#### Technical service bulletins

Datasheet - FNQ-30



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com

Reserved.

Eaton is a registered trademark.

All other trademarks are © 2024 Eaton. All Rights property of their respective owners.



Eaton.com/socialmedia