



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



FNQR25 25A 600V TD Class CC Fuse

Bussmann Fuses

Catalog Number	FNQR25
Manufacturer	Bussmann Fuses
Description	Eaton Bussmann Series Class CC Fuse, FNO, Time-Delay, Dual-Element Current Limiting Fuse, 25 A, Rejection Style Fuse, Interrupting Rating Of 200KA At 600vac
Weight per unit	0.0200 (lbs/each)
Product Category	Small Dimension Fuses

Features

class	Class CC
media	Yes

Descriptions

Description	25A 600V TD CLASS CC FUSE
extra long description	BUSS FNO-R-25 CLASS CC TIME DELAY
Features	Bussmann's Class CC fuses set the standard in Class CC fuse performance in the industry. Recognized for their superior performance, Bussmann has the right product for your circuit and equipment protection needs. These branch circuit rated, 600v, 200,000a IR fuses offer exceptional protection in the smallest package of any UL class of fuses. Choose from the ultimate protection provided by our Low Peak LP-CC fuses, the time delay of our FNO-R's for your control transformer and similar control applications or
Long Description	Eaton Bussmann Series Class CC fuse, FNO, time-delay, dual-element current limiting fuse, 25 A, rejection style fuse, interrupting rating of 200kA at 600Vac
Product Type	Class CC Time Delay

Manufacturer Information

Brand	Eaton
GTIN	00051712497138
Manufacturers Part Number	FNO-R-25
UPC	051712497138

Taxonomies, Classifications, and Categories

Category Description	MIDGET FUSES
----------------------	--------------

Packaging

Carton	10
Weight Per each	0.02