# Eaton FNQ-R-7

## Catalog Number: FNQ-R-7

Eaton Bussmann series FNQ-R fuse, 7 A, Class CC, Nonindicating, 12 sec at 200%, 200 kAIC, Nickel-plated brass endcap|Melamine tube, Standard, 600 V



## General specifications

Product Name Eaton Bussmann series FNQ-R fuse UPC

051712558259

Product Length/Depth 0.41 in

Product Width 0.41 in

Warranty Not Applicable Catalog Number FNQ-R-7

EAN 5027590449809

Product Height 1.5 in

Product Weight 0.15 lb

Compliances RoHS Compliant CE Marked



## **Electrical Ratings**

#### Amperage Rating

7 A

Voltage rating 600 V

## **Physical Details**

Туре

Current-limiting high inrush time-delay fuse

## **General Information**

#### Application

Line protection, small control transformers, industrial control, branch circuits

Special features

Rejection style

#### Resources

Catalogs Bussmann series complete full line catalog no. 1007

Multimedia Bussmann series Fuseology

Specifications and datasheets Eaton Specification Sheet - FNQ-R-7

Technical data sheets FNQ-R-7~CLASS CC TIME DELAY

Technical service bulletins Datasheet - FNQ-30



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com © 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

Eaton.comAll other trademarks are© 2023 Eaton. All Rightsproperty of their respectiveReserved.owners.



Eaton.com/socialmedia