

Eaton Bussmann series FNQ-R fuse

FNQ-R-8

UPC:051712497060

Dimensions:

- **Height:** .41 IN
- **Length:** 1.5 IN
- **Width:** .41 IN

Weight:.15 LB

Warranties:

- Not Applicable

Specifications:

- **Type:** Current-limiting, high inrush, time delay
- **Special Features:** Rejection style
- **Application:** Line protection, small control transformers, industrial control, branch circuits
- **Voltage Rating:** 600V
- **Amperage Rating:** 8A
- **Interrupt Rating:** 200 kAIC
- **Class:** Class CC
- **Connection:** Ferrule end X ferrule end
- **Material Type:** Melamine tube
- **Packaging Type:** Standard
- **Diameter:** .40625 IN
- **Fuse Indicator:** Non Indicating
- **Response Time:** 12s at 200%

Supporting documents:

- [Product Catalog](#)
- [CLASS CC TIME DELAY](#)
- [Product Datasheet](#)

Certifications: No Data

Product compliance:

- RoHS Compliant
- CE Marked

