# Eaton FNQ-R-9

# Catalog Number: FNQ-R-9

Eaton Bussmann series FNQ-R fuse, 9 A, Class CC, Nonindicating, Ferrule end x ferrule end, 12 sec at 200%, 200 kAIC, Melamine tube, Standard, 600 V

# General specifications

Product Name	Catalog Number
Eaton Bussmann series FNQ-R fuse	FNQ-R-9
UPC	EAN
051712497084	5027590449830
Product Length/Depth	Product Height
0.41 in	1.5 in
Product Width	Product Weight
0.41 in	0.15 lb
Warranty Not Applicable	Compliances RoHS Compliant CE Marked



# **Electrical Ratings**

#### **Amperage Rating**

9 A

Voltage rating 600 V

# General Information

#### Application

Line protection, small control transformers, industrial control, branch circuits

Connection

Ferrule end x ferrule end

# Special features

Rejection style

### **Physical Details**

Туре

Current-limiting high inrush time-delay fuse

# Resources

#### Catalogs

Bussmann series complete full line catalog no. 1007

Multimedia

Bussmann series Fuseology

Specifications and datasheets Eaton Specification Sheet - FNQ-R-9

Technical data sheets FNQ-R-9~CLASS CC TIME DELAY

Technical service bulletins Datasheet - FNQ-30



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com © 2023 Eaton. All Righ Reserved.

Eaton is a registered trademark.

Eaton.comAll other trademarks are© 2023 Eaton. All Rightsproperty of their respectiveReserved.owners.



Eaton.com/socialmedia