

Single (Thin) Wall Tubing: 3M™ FP-301 Thin-Wall Tubing



3M™ Heat Shrink Thin-Wall Tubing FP-301 (3/8 Inch)

Ordering Size: 3/8" (9,52 mm)

Expanded I.D. (Min.): 0.375" (9,53 mm)

Recovered I.D. (Max.): 0.187" (4,75 mm)

Recovered Wall Thickness (Nominal): 0.025" (0,64 mm)

Material	Polyolefin
Shrink Ratio	2:1
Operating Temperature	-67 to 275°F (-55 to 135°C)
Voltage	600 Volts Max.
RoHS 2011/65/EU	Yes
Application Specifications	SAE-AMS-DTL-23053/5, Class 1, 2; AMS-3636, AMS-3637
Agency Approvals	
Manufacturing Origin	



Order No.	UPC	Color	Format	Flame Retardant	Case Qty.
FP301-3/8-6"-Black-200 Pcs	051128-59892	Black	6" (152,4 mm) pieces	Yes	200 pcs
FP301-3/8-6"-Black-10-10 Pc Pks	051128-60127	Black	6" (152,4 mm) pieces	Yes	10/pk, 10 pks
FP301-3/8-6"-Clear-10-10 Pc Pks	051128-60128	Clear	6" (152,4 mm) pieces	No	10/pk, 10 pks
FP301-3/8-48"-Black-12 Pcs	051128-59584	Black	48" (1,22 m) sticks	Yes	12 pcs
FP301-3/8-48"-Black-125 Pcs	051128-59837	Black	48" (1,22 m) sticks	Yes	125 pcs
FP301-3/8-48"-Blue-12 Pcs	051128-59589	Blue	48" (1,22 m) sticks	Yes	12 pcs
FP301-3/8-48"-Clear-12 Pcs	051128-59585	Clear	48" (1,22 m) sticks	No	12 pcs
FP301-3/8-48"-Clear-125 Pcs	051128-59853	Clear	48" (1,22 m) sticks	No	125 pcs
FP301-3/8-48"-Green-12 Pcs	051128-59590	Green	48" (1,22 m) sticks	Yes	12 pcs
FP301-3/8-48"-Red-12 Pcs	051128-59587	Red	48" (1,22 m) sticks	Yes	12 pcs
FP301-3/8-48"-White-12 Pcs	051128-59586	White	48" (1,22 m) sticks	Yes	12 pcs
FP301-3/8-48"-Yellow-12 Pcs	051128-59588	Yellow	48" (1,22 m) sticks	Yes	12 pcs
FP301-3/8-48"-Black-Hdr-12 Pcs	051128-59661	Black	48" (1,22 m) sticks w/ Hdr Label	Yes	12 pcs
FP301-3/8-48"-Blue-Hdr-12 Pcs	051128-59666	Blue	48" (1,22 m) sticks w/ Hdr Label	Yes	12 pcs
FP301-3/8-48"-Clear-Hdr-12 Pcs	051128-59662	Clear	48" (1,22 m) sticks w/ Hdr Label	No	12 pcs
FP301-3/8-48"-Green-Hdr-12 Pcs	051128-59667	Green	48" (1,22 m) sticks w/ Hdr Label	Yes	12 pcs
FP301-3/8-48"-Red-Hdr-12 Pcs	051128-59664	Red	48" (1,22 m) sticks w/ Hdr Label	Yes	12 pcs
FP301-3/8-48"-White-Hdr-12 Pcs	051128-59663	White	48" (1,22 m) sticks w/ Hdr Label	Yes	12 pcs
FP301-3/8-48"-Yellow-Hdr-12 Pcs	051128-59665	Yellow	48" (1,22 m) sticks w/ Hdr Label	Yes	12 pcs
FP301-3/8-25'-Black-Reel	054007-40063	Black	25' (7,62 m) reel	Yes	1 reel
FP301-3/8-100'-Black-Spool	051135-35580	Black	100' (30,48 m) spool	Yes	3 spools
FP301-3/8-Blue-100'	051135-35583	Blue	100' (30,48 m) spool	Yes	3 spools
FP301-3/8-100'-Clear-Spool	051135-35585	Clear	100' (30,48 m) spool	No	3 spools
FP301-3/8-Green-100'	051135-37643	Green	100' (30,48 m) spool	Yes	3 spools
FP301-3/8-Red-100'	051135-35582	Red	100' (30,48 m) spool	Yes	3 spools
FP301-3/8-White-100'	051135-35581	White	100' (30,48 m) spool	Yes	3 spools
FP301-3/8-Yellow-100'	051135-35584	Yellow	100' (30,48 m) spool	Yes	3 spools
FP301-3/8-200'-Black-Spool	054007-08491	Black	200' (60,96 m) spool	Yes	3 spools
FP301-3/8-200'-Clear-Spool	054007-08529	Clear	200' (60,96 m) spool	No	3 spools