




# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1732 South Business 287  
75110-0000, TX Corsicana  
Phone: 903-872-9696  
Fax: 903-872-9980



## FP54835H0ECO T5 48" Mini Bipin High Output Fluorescent Lamp

*Sylvania-Ledvance*

Catalog Number	FP54835H0ECO
Manufacturer	Sylvania-Ledvance
Description	54W, T5 Pentron High Output (Ho) Fluorescent Lamp, 3500K Color Temperature, Rare Earth Phosphor, 85 Cri, Ecologic
Weight per unit	0.2700 (lbs/each)
Product Category	Linear Fluorescent Straight La

### Features

amperage rating	Ballast Dependent
average life	30000
Base	Miniature Bipin
bulb type	T5
Lamp Type	PROGRAMMED RAPID START
lumens	4450 Initial Lumens at 25 Degrees C
Shape	T5
start type	Programmed Rapid Start
total harmonic distortion	Ballast Dependent
Voltage Rating	Ballast Dependent
Wattage	54

### Material, Color, and Finish

color rendering index (cri)	85
color temperature	3500
Finish	Phosphor Coated

### Dimensions and Weight

Diameter	0.625
----------	-------

### Descriptions

Description	T5 48" MINI BIPIN HIGH OUTPUT FLUORESCENT LAMP
extra long description	SYL FP54/835/HO/ECO/20904 FP54835HO
Long Description	54W, T5 PENTRON high output (HO) fluorescent lamp, 3500K color temperature, rare earth phosphor, 85 CRI, ECOLOGIC
Product Type	FP54835HOECO 40/CS 1/Sku

### Manufacturer Information

Brand	SYLVANIA
GTIN	00046135209048
Manufacturers Part Number	FP54/835/HO/ECO/20904
UPC	046135209048



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1732 South Business 287  
75110-0000, TX Corsicana  
Phone: 903-872-9696  
Fax: 903-872-9980

## Taxonomies, Classifications, and Categories

Category Description ..... Fluorescent

Type ..... FLUORESCENT

## Packaging

Carton ..... 1

Package ..... 40

Weight Per each ..... 0.27

## Uses, Certifications, and Standards

Application ..... Commercial/Residential