



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

537 N 40th St
72762-0000, AR Springdale
Phone: 479-361-2266
Fax: 479-361-9188



FP54850H0ECO 48" 54W T5HO 5000K Fluorescent Lamp

Sylvania-Ledvance

Catalog Number	FP54850H0ECO
Manufacturer	Sylvania-Ledvance
Description	54W, T5 Pentron High Output (Ho) Fluorescent Lamp, 5000K Color Temperature, Rare Earth Phosphor, 85 Cri, Ecologic
Weight per unit	0.2700 (lbs/each)
Product Category	Linear Fluorescent Straight La

Features

amperage rating	Ballast Dependent
Base	Miniature Bipin
beam angle	Universal
bulb type	T5
Lamp Type	PROGRAMMED RAPID START
lumens	4375 Initial Lumens at 25 Degrees C
Shape	T5
total harmonic distortion	Ballast Dependent
Voltage Rating	Ballast Dependent
Wattage	54

Material, Color, and Finish

color rendering index (cri)	85
-----------------------------	----

Descriptions

Description	48" 54W T5HO 5000K FLUORESCENT LAMP
extra long description	SYL FP54/850/HO/ECO/20949 FP54850HO
Long Description	54W, T5 PENTRON high output (HO) fluorescent lamp, 5000K color temperature, rare earth phosphor, 85 CRI, ECOLOGIC
Special Features	COOL WHITE

Manufacturer Information

Brand	SYLVANIA
GTIN	00046135209499
Manufacturers Part Number	FP54/850/HO/ECO/20949
UPC	046135209499

Taxonomies, Classifications, and Categories

Category Description	Fluorescent
Type	FLUORESCENT

Packaging

Carton	1
Package	40
Weight Per each	0.27



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

537 N 40th St
72762-0000, AR Springdale
Phone: 479-361-2266
Fax: 479-361-9188

Uses, Certifications, and Standards

standard

ANSI C78.81 - 2001
