

Eaton Bussmann series FRN-R fuse

FRN-R-15

UPC:051712101745

Dimensions:

- **Height:** .56 IN
- **Length:** 2 IN
- **Width:** .56 IN

Weight:.5 LB

Warranties:

- Not Applicable

Specifications:

- **Type:** Current-limiting, time delay
- **Application:** Combination starters, motor control centers, machinery disconnects, power panelboards
- **Voltage Rating:** 250 Vac, 125 Vdc
- **Amperage Rating:** 15A
- **Interrupt Rating:** 200 kAIC at 250 Vac, 20 kAIC at 125 Vdc
- **Class:** Class RK5
- **Connection:** Ferrule end X ferrule end
- **Packaging Type:** Standard
- **Diameter:** .56 IN
- **Fuse Indicator:** Non Indicating
- **Response Time:** 8s at 500%
- **Number Of Elements:** Dual

Supporting documents:

- [FUSETRON DUAL-ELEMENT CLASS RK5](#)
- [Product Datasheet](#)

Certifications: No Data

Product compliance:

- CE Marked

