Eaton FRN-R-20

Catalog Number: FRN-R-20

Eaton Bussmann series FRN-R fuse, 20 A, Dual, Class RK5, Nonindicating, Ferrule end x ferrule end, 8 sec at 500%, 20 kAIC at 125 Vdc|200 kAIC at 250 V, Standard, 250 V, 125 Vdc



General specifications

Product Name

Eaton Bussmann series FRN-R fuse

UPC 051712101752

Product Height 1.56 in

Product Weight 0.9 lb

Compliances CE Marked Catalog Number FRN-R-20 Product Length/Depth

1.56 in

Product Width 1.56 in

Warranty

Not Applicable



Electrical rating

Amperage Rating

20 A

Interrupt rating

20 kAIC at 125 Vdc 200 kAIC at 250 Vac

Response time

8 sec at 500%

Voltage rating

250 Vac, 125 Vdc

Physical details

Number of elements

Dual

Packaging type

Standard

General information

Class

Class RK5

Connection Ferrule end x ferrule end

Fuse indicator

Non-indicating

Resources

Multimedia Bussmann series Fuseology

Specifications and datasheets Eaton Specification Sheet - FRN-R-20

Technical data sheets FRN-R-20~FUSETRON DUAL-ELEMENT CLASS RK5

Technical service bulletins

Datasheet - FNQ-30



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com © 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

Eaton.comAll other trademarks are© 2023 Eaton. All Rightsproperty of their respectiveReserved.owners.



Eaton.com/socialmedia